for monitoring risk situations.















MONILOG®

## **MicroShockDetector**



















- Registers the 200 largest shock events in the X, Y, Z direction
- Saves up to 10 curve progressions of the largest shocks
- Intelligent signal filtering and evaluation
- Indicates limit value overruns with alarm LED
- Continuous temperature recording
- Intuitive operation, extremely long and independent operating time
- Communication via USB
- Easy configuration and evaluation with license-free PC software
- Configurable recording time over start-stop time
- Easy mounting with adhesive pad, screws or magnetic feet







## MicroShockDetector

#### ECONOMIC SOLUTION - EVEN FOR ONE-TIME USE

High-sensitivity devices, e.g. large, superconducting magnets in medical technology, need a safe and demonstrable protection during transport or during storage. • The compact *MONILOG* • *MicroShockDetector* provides the best services. • It is smaller than a smartphone and weighs only 180 grams. • The measuring device reliably stores all data on shocks of every dimension, assigns them to acceleration classes, provides curve progressions and reports alarms

as soon as limit values are exceeded. • In addition, the temperature is monitored. • The switch-on time of the *MicroShockDetector* is easy to configure. • All data can be read out via the USB port, transferred to a PC and evaluated. • The device is quickly installed and dismantled with adhesive pads, screws or supplied magnetic holding feet. • Due to the good economic and ecological parameters, the data logger can also be used only once.























Technical data of MONILOG® MicroShockDetector	
Shock parameters:	200 data records with the highest space vector amplitude, of which the 10 highest values with a curve-plots over 4 s, resolution 2 ms
Acceleration sensor:	3D-MEMS, measuring range ±8 g, 10mg resolution, accuracy: ±(0.2g and 2% measurement value), registering threshold from 0.25g lower limit frequency 1 Hz upper filter limit frequency 25 Hz fixed-adjusted
Shock classification:	Subdivision of shocks according to space vector amplitude into classes, number of shocks not limited $>0.25$ g, $>0.5$ g, $>1$ g, $>1.5$ g, $>2$ g, $>3$ g, $>4$ g, $>5$ g
Temperature measurement:	-40°C to +65°C ±1 K, 100,000 measurement values
Indication:	2 LEDs for status and alarm limit-value overshooting
Operating elements:	1 button for status indicator, ON/OFF switching with password protection
Connections:	Mini USB 2.0
Operating and storage conditions:	-40°C to +65°C, max. 98% rel. humidity
Power supply:	1 replaceable lithium cell, 3.6 V type LR06 (AA, Mignon), lithium content ~0.7g runtime typically 3 years in switch-on time period (depending on the device configuration)
Data storage:	Receipt of measuring data independent of battery status for a minimum of 10 years
Dimensions:	106x48x33 mm (LxWxH), 126x48x40 mm (LxWxH with magnetic feet)
Housing:	Plastic housing with stainless steel base
Weight:	approx. 172 g (258 g total if mounted on magnetic feet)
Protection type:	IP 67
Programmable parameters:	X, Y, Z registering threshold, X, Y, Z alarm threshold, minimum shock duration, temperature-measurement interval Start-Stop time (switch-on time period), password protection by means of free Windows software
Conformity:	Device certification according to CE, UKCA, IC, FCC, RoHS, REACH, WEEE Use according to IEEE C 57:150-2012





# WHAT ARE YOU LOGGING FOR?

MONILOG® Risk Loggers measure, signal and document the external influences that threaten the value and functional capability of your damageable items.

We offer the ideal product design, software and sensor system for each and every customer requirement:





















Where are your freight items located? Which levels of stress are and have the items been exposed to?





Are the ambient conditions correct for your stored items?
Were they and will they remain stable?





Do mechanical factors put operation of your offshore plant at risk? When do you, as the operator, need to intervene?





Which device maps your particular risk profile? Our product finder provides the answer and sets the course for specific modifications or for new developments. Product finder online: www.monilog.com/productfinder